



06152045

RCK 15 - Self centring

2D Technical Drawing

Dynamic 3D View

Technical Specifications

Part number (CODE)	06152045
Ød (DD) mm	45
ØD (D) mm	80
L1 (L1) mm	20
L2 (L2) mm	25
L3 (L3) mm	33
L (L) mm	41
Maximum torque Mt (MT) Nm	1620
Clamping pressure - Shaft (CPS) N/mm ²	212
Clamping pressure - Hub (CPH) N/mm ²	120
Clamping screws DIN 912 MAT. 12.9 - Num. (CSN)	7
Clamping screws DIN 912 MAT. 12.9 - Type (CST)	M8x25
Clamping screws DIN 912 MAT. 12.9 - Torque (CSTQ) Nm	41
Extraction thread - Type (ETT)	M8
Extraction thread - Num. (ETN)	3
Weight (WEIGHT) kg	0.80