

1100-245681

Manual bending tool set

hydraulic, reinforced version, in L-BOXX® 136

Code	ETIM
2963558	EC002189
EAN	UNSPSC
4017981012461	27-11-25-01
Country of origin	eCl@ss
Spain	21-04-16-03
Customs tariff number	
82055980	



Article description

- Dimensions from 6 to 22 mm Ø to 90°
- Soft copper tubes EN 1057 up to 22 mm (also heat insulated)
- Composite pipes up to 20 mm
- Precision steel tubes EN 10305-3 (DIN 2394) up to 18 x 2 mm
- Annealed stainless steel tubes up to 18 x 1.2 mm
- With 10 bending moulds for tubes with Ø 6, 8, 10, 12, 14, 15, 16, 18, 20 and 22 mm and corresponding counter holders
- Hydraulic drive without great effort
- In GEDORE L-BOXX® 136 No. 1100 L
- Dimensions: W 442 x D 357 x H 151 mm

Article parts list

1 basic unit, hydraulic No. 245670, 10 aluminium bending formers, for pipes of Ø 6, 8, 10, 12, 14, 15, 16, 18, 20, 22 mm, 1 counter-support Ø 6-12 mm, 2 counter-supports reinforced Ø 14-17, 18-22 mm, 1 pipe cutter 3-35 mm Ø No. 2180 3, + GEDORE L-BOXX® 136 No. 1100 L

Article information

Contents (Qty of pieces)	1	Total width [mm]	442 mm
Net weight [kg]	9,62 kg	Total height [mm]	151 mm
Total length [mm]	357 mm		