

HOSE COILS

Reinforced SURFLEX PVC hose - Coil



Part number	Length (m)	Radius of curve (mm)	Max. operating pressure (bar)	Net weight (Kg)	Color
SURFLEX 8	50.00	56.00	15.00	0,1	Blue
SURFLEX 8C30	30.00	56.00	15.00	0,094	Blue
SURFLEX 9	50.00	63.00	15.00	0,11	Blue
SURFLEX 10	50.00	70.00	15.00	0,126	Blue
SURFLEX 10C30	30.00	70.00	15.00	0,132	Blue
SURFLEX 13	50.00	89.00	15.00	0,176	Blue

Part number	Ø int/ext (mm)
SURFLEX 8	8.00 / 13.00
SURFLEX 8C30	8.00 / 13.00
SURFLEX 9	9.00 / 14.50
SURFLEX 10	10.00 / 15.00
SURFLEX 10C30	10.00 / 15.00
SURFLEX 13	12.70 / 19.00