

PRODUCT SHEET 54982E



EXACOMPTA
PARIS

Reference code	54982E
designation	Forever Recycled Ring Binder, A4, 2 O-rings, 40mm spine - Light blue
Collection	Forever®
Material	Recycled Paper
Thickness	18/10E
Product size	320x260 mm
Colour	Light blue
Product size (LxIhx)	320 x 260 x 40 mm
Unit weight	280 g
Product volume	3.328 dm ³
Ean code	3130630549826
Units per box	10
Size pack (LxIhx)	445 x 155 x 335 mm
Box weight	3 065 g
Pack volume	23.107 dm ³
EAN pack	3130632549824
Units per palette	720
Size pallet (LxIhx)	1200 x 800 x 2095 mm
Palette weight	282 840 g
Pallet volume	2 011 dm ³



DIN
6738



www.blauer-engel.de/uz14b



Brand : Exacompta

Size : A4

Product type : Ring binder

Interior material : Recycled Paper

Spine (mm) : 40

Type : ring binder

Number of rings : 2

Rings : 30mm

Capacity (sheets 80 gr.) : 275

Ring type : O-ring



The Forever Ring Binder is made from 100% recycled paper covering 100% recycled board. 2 O rings which are 30mm in size.

The spine is 40mm in size.

Size of Ring Binder 32x26cm

The Ring Binder can hold A4 sized documents

Blue Angel certified

Label on spine

Product sheet related to environmental qualities or features: 54982E

Product has Datasheet	Yes
Product has performance claims	Yes
REACH annex XIV relevant	No
REACH annex XIV > 0,1%	No
REACH annex XVII relevant	No
POP relevant	No
Major cost origin	FR
Prod reduced energy consump	Yes, for all products
Product has recycled content	Yes
% recycled Post Consumer waste	88
% recycled Pre Consumer waste	
Product is vegan	not known
Product is sustainable because	DIN6738 certified
Product is plastic free	Yes
Weight of plastic in product	0
Plastic free packaging	Yes
Weight of plastic in packaging	0
Product has ecodesign approach	Yes
Is product compostable?	not compostable
Is product recyclable?	Yes
% Recyclability	100
Easy to sep waste/recyclable	Yes
Product easy to disassemble	No
Product can be repaired	No
Spare parts available	No
Refillable	No
Primary packaging is mono mat	Yes
Product is reusable	Yes
Prod second-hand/refurbished	No
Factory enviro management syst	Non certified EMS