



DCF813S2

10.8 Volt Impact Wrench

Selling Proposition

- 10.8V Compact Cordless Impact Wrench
- Compact, durable design delivers 130Nm of torque
- All metal gearing for efficient power transmission and long tool life
- Aluminium front housing provides greater heat dispersion increasing motor life
- Parabolic switch profile allowing for greater control over speed
- 3 LED 'Halo' ring provides maximum illumination to work piece

Standard Equipment

- 40 min charger
- 2 Batteries
- Kit Box

Warranty Specifications

- 3 year limited warranty
- 30 Day No Risk Satisfaction Guarantee
- 1 Year Free Service Contract

Specifications	
Voltage	10.8 V
Battery Capacity	1.3 Ah
Bit Holder	3/8" Anvil
Power Output	147 Watts
No Load Speed	0-2450 rpm
Impacts per Minute	3400 ipm
Max. Torque	130 Nm