

**Datasheet**

# Type D Female Coupler x BSPP Female End



Image representative of range

## Technical Specifications:

Specifications	
Gasket	Buna-N Nitrile
Temperature Rating	-40° C to +100° C

## Features & Benefits:

- **Manufactured to interchange with all products produced to MIL-C-27487F**
- **BSP male threads to BS21 (Taper)**
- **BSP female threads to BS2779 (Parallel)**

## Pressure Ratings:

- **Recommendations based on the use of mating fittings at ambient temperature 20°C with standard Nitrile seals installed.**

RS Article	Size	Material	Working Pressure
362-6756	1"	Aluminium	17.2 bar
233-3368	1"	Polypropylene	7 bar
307-241	1"	Stainless Steel	17.2 bar
362-6762	1.1/2"	Aluminium	17.2 bar
233-3374	1.1/2"	Polypropylene	7 bar
307-257	1.1/2"	Stainless Steel	17.2 bar
362-6778	2"	Aluminium	17.2 bar
233-3380	2"	Polypropylene	7 bar
307-263	2"	Stainless Steel	17.2 bar