

Endress+Hauser FTL325P-H3E3

Nivotester FTL325P



Level instrument, point level. Input: 1/3-channel, 2-wire PFM.

Picture for reference only. Product appearance may vary based on configuration

Configuration of FTL325P-H3E3:

Approval:	H	ATEX II (1)GD [Ex ia] IIC,WHG, SIL,IECEX [Ex ia] IIC
Housing:	3	Rail mounting, 45mm, 3-channel
Power Supply:	E	20-30VAC/20-60VDC
Switch Output:	3	3x SPDT level + 1x SPST alarm

Alternative part number: FTL325P-H3E3