

Datasheet

Flexible articulated arms with optional LED light for desktop use.



The wide range of volume LEV extraction accessories including 32 or 50mm stainless steel, black ESD and LED Light extraction Arms. The arms can be mounted into the unique flip top mount and can easily moved to the best angle for your application.

The LED light arms have 8 LED lights at the end of the funnel lighting up your work piece, these new arms allow for a clearer work space and a bright clean light work area.

The black version is made from ESD anti-static plastic primarily for the electronics industry.

LED LIGHT ARMS - STANDARD FEATURES:

- High energy efficiency and maintenance-free.
- Eight powerful LED provide upto 58 Lumens.
- Low energy consumption.
- Long lifetime.
- 12 Volt DC operation.

FLEXIBLE ARMS - STANDARD FEATURES:

- Maintenance-free.
- Long lifetime.
- Quick and easy setup.



Tip and Volume Extraction Accessories

BOFA's wide range of volume LEV extraction accessories range from arms with diameters of 32mm for intricate soldering up to 75mm arms for heavy duty applications such as transformer production, to down draft trays and table top cowls for specific production demands.

PART NUMBERS		
Number reference to photo	Part No.	Description
1	764-5773	38mm Stainless Steel ESD Stay Put Arm with Nozzle - 800mm
2	764-5776	38mm Stainless Steel ESD Stay Put Arm with Funnel - 800mm
3	764-5764	Light Arm - Black 38mm ESD Stay Put Arm with Funnel
4	*	Automatic Flush System Seal for 32mm and 50mm
5	*	38mm ESD Stay Put Arm with Nozzle
6	*	38mm ESD Stay Put Arm with Funnel

* **Optional features** are available on request.
Please contact RS Components for more information.

