

Datasheet

RS Pro DC Geared Motor, 12 V dc, 60 Ncm, 8 rpm, 2.1 W

RS Stock No: **255-9649**



Product Details

RS Pro DC geared motor delivers 8 rpm output using 12 V dc supply voltage. This brushed motor has a shaft of 6 mm diameter and produces power up to 2.1 W. The ironless rotor provides linear speed-torque performance.

Features and Benefits

- Suitable for use with peristaltic pumps
- The reversible motor has an ironless rotor giving linear speed-torque performance
- Superior speed



ENGLISH

Specifications:

Core Construction	Ironless
DC Motor Type	Brushed
Gearhead Type	Spur
Standards Met	RoHS Compliant
Depth	96.5 mm
Length	38 mm
Shaft Diameter	6 mm
Width	30.5 mm
Dimensions	96.5 x 30.5 x 38 mm
Maximum Output Torque	60 Ncm
Output Speed	8 rpm
Power Rating	2.1 W
Supply Voltage	12 V dc