

WG-88FP IRONPRO

The Wonder Grip® WG-88FP IronPro is a 13-gauge glove delivering ISO 13997 level D and ANSI/ISEA 105 level A4 cut protection, constructed with a liner made from Tsunooga™ high-performance polyethylene (HPPE) fibre. The Tsunooga™ fibre provides high tensile strength and durability while remaining lightweight, flexible, and comfortable for extended wear.

With its single nitrile coating, the WG-88FP IronPro offers excellent grip and flexibility in dry, slightly wet, or oily environments. In addition, thermo-plastic rubber (TPR) reinforcements are integrated on the back of the hand, providing robust impact protection for knuckles and the back of the hand while maintaining comfort and freedom of movement.

The Wonder Grip® WG-88FP IronPro combines advanced cut resistance, impact protection, and ergonomic performance with Wonder Grip® renowned gripping power, making it the ideal choice for professionals seeking innovative hand protection in demanding conditions.



KEY FEATURES

- ✓ Soft flexible liner, engineered with Tsunooga® Japanese yarn to offer cut level A4/D protection
- ✓ Reinforced thumb crotch for increased protection and extended use-life
- ✓ IT-compatible with touch screen functionality for improved working conditions.
- ✓ Robust, soft, and stretchable TPR shielding ensuring advanced protection while maintaining unhindered motion.

TYPE OF PROTECTION

- Heat resistance
- Cut resistance

APPLICATIONS

- Metallurgy
- Airports and ports
- Waste management
- Construction-and-public-works
- Railways
- Mining industry

NORMS AND CERTIFICATIONS

EN 388



4X42DP

EN 407



X1XXXX



CUT



INFORMATIONS

- **Coating level** | Nitrile, Palm coated
- **Support** | Spandex, Mineral fiber, HPPE, Polyester, UHMWPE : Tsunooga™
- **Gauge** | 13
- **Size** | 6, 7, 8, 9, 10, 11
- **Packaging** | 12 pairs / polybag, 72 pairs / box

TECHNOLOGIES



Tsunooga®

