



Part Number : [1200868666](#)
Product Description : Nano-Change (M8)
Single-Ended Cordset with Knurled Hexnut, 5
Poles, B-Coded, Female (Straight) to Pigtail, 24
AWG, Black TPU WSOR Cable, 10.0m (32.81')
Length
Series Number : 120086
Status : Active
Product Category : Circular Industrial
Cordsets
Engineering Number : 405000B41M100



Documents & Resources

Drawings
[1200868666_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead... per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120086
Description	Nano-Change (M8) Single-Ended Cordset with Knurled Hexnut, 5 Poles, B-Coded, Female (Straight) to Pigtail, 24 AWG, Black TPU WSOR Cable, 10.0m (32.81') Length
IP Rating	IP67
Product Name	Nano-Change (M8)
Protocol	N/A
Type	Single Ended
UPC	889056003711

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	30V

Physical

Cable Diameter	5.30mm (.209")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Black
Connector End A	Nano-Change (M8)
Connector End B	Pigtail
Coupling Style	Knurled Hexnut, Threaded
Gender	Female-Pigtail
Keyway	B-Coded
LED Indicator	None
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Contact	Brass

Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	1245.000/g
Orientation	Straight to Pigtail
Poles	5
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	UL 21215
Wire Size (AWG)	24

This document was generated on Mar 27, 2025