

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00	REVISED PER ECO-11-004835	11MAR11	RK	HMR

4-40 HEX NUT
QTY: 2

SCREW
QTY: 2

MOUNTING SCREW
QTY: 2

SEE TABLE FOR SIZE IDENTIFICATION LETTER

CABLE CLAMP
QTY: 2

TEXTURED FINISH

ASSEMBLED VIEW
SCALE 1:1

67.16±0.38 [2.644±.015]

22.86±0.38 [.900±.015]

48.77±0.38 [1.920±.015]

61.11±0.38 [2.406±.015]

18.54±0.38 [.730±.015]

① SCREW: CARBON STEEL.
MOUNTING SCREW & HEX NUT: CARBON STEEL.
CABLE CLAMP: ZINC.

② SCREWS, MOUNTING SCREWS & HEX NUTS: ZINC PLATE 5.08µm-10.16µm [.000200-.000400] THICK, CLEAR CHROMATE COATING.
CABLE CLAMP: 5.08µm [.000200] MIN NICKEL OVER 5.08µm [.000200] MIN COPPER.

NECK SIZE I.D.	CABLE DIA	PART NO.
I	9.53 [.375]	5745175-6
L	11.43 [.450]	5745175-5
O	13.34 [.525]	5745175-4
S	15.24 [.600]	5745175-3
U	17.15 [.675]	5745175-2
V	19.05 [.750]	5745175-1

**COPYRIGHT 2005
TE CONNECTIVITY CORP
ALL RIGHTS RESERVED**

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. HENNY 8-13-05	TE TE Connectivity		
DIMENSIONS: MM[INCHES]		CHK C. ROHDE 8-13-05			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. WALMSLEY 8-13-05	NAME CABLE CLAMP KIT, UNASSEMBLED, SIZE 5, 50 POSITION, 180DEG, AMPLIMITE SERIES		
0 PLC ± - 1 PLC ± - 2 PLC ± .013 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC -	SIZE A2	CAGE CODE 00779	DRAWING NO C=5745175
MATERIAL ①	FINISH ②	APPLICATION SPEC -	WEIGHT -	RESTRICTED TO -	
CUSTOMER DRAWING			SCALE 2:1	SHEET 1 of 1	REV P

1471-9 (3/11)

5745175