

POLYAMIDE SPIRAL HOSES

Polyamide recoils with swiveling male fittings



Part number	Length (m)	Temperature min/max (°C)	Max. operating pressure (bar)	Net weight (Kg)	Color
SPIC 62	2.50	-20.00 / 90.00	10.00	0,178	Blue
SPIC 65	5.00	-20.00 / 90.00	10.00	0,29	Blue
SPIC 610	10.00	-20.00 / 90.00	10.00	0,45	Blue
SPIC 82	2.50	-20.00 / 90.00	10.00	0,23	Blue
SPIC 85	5.00	-20.00 / 90.00	10.00	0,35	Blue
SPIC 810	10.00	-20.00 / 90.00	10.00	0,6	Blue

Part number	Ø int/ext (mm)
SPIC 62	6.00 / 8.00
SPIC 65	6.00 / 8.00
SPIC 610	6.00 / 8.00
SPIC 82	8.00 / 10.00
SPIC 85	8.00 / 10.00
SPIC 810	8.00 / 10.00