

Eaton 138361

Catalog Number: 138361

Eaton xEffect SASY 60i Enclosures Switch- & Controlgear Enclosure. Conductor connection terminal M10 for 10mm

General specifications



Product Name	Catalog Number
Eaton xEffect SASY 60i busbar terminal	138361
EAN	Product Length/Depth
4015081351411	47 mm
Product Height	Product Width
42 mm	38 mm
Product Weight	Compliances
0.362 kg	RoHS conform

Product specifications

Used with

All 10 mm thick flat busbars
Double T profile

Special features

With integrated retaining spring, open terminal chamber and captive terminal screw

Type

185 mm system
60 mm system
Compact system
Connection

Width clamp

38 mm

Terminal contact area

10 mm with M10 bolt

Busbar thickness - max

10 mm

Busbar thickness - min

10 mm

Busbar width - max

0 mm

Busbar width - min

0 mm

Conductor cross section - max

0 mm²

Rated operational current (I_e) - max

630 A

Functions

Universal conductor connection terminal
Connections

Rated operation current (I_e)

630 A

Suitable for

Round conductor connection
Flat rail

Rated operational current

Resources

Brochures

[eaton-xeffect-sasy60i-customer-success-story-css-wagner-mueller-en-us.pdf](#)

Catalogs

Product Range Catalog Switching and protecting motors
[eaton-xeffect-sasy-60i-fk4300-1167gb-en-us.pdf](#)

Certification reports

[eaton-xeffect-sasy-60i-declaration-of-conformity.pdf](#)

Drawings

[eaton-control-panels-xeffect-sasy-enclosure-3d-drawing-011.eps](#)

630 A

Terminal capacity (conductor)

Cable lugs M10



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia