



tested to work

15501-231 Outer Shell Jacket

waterproof

MASCOT® SAFE SUPREME



100% polyester
210 g/m²



Ripstop. The product is certified to retain its qualities with 50 domestic washes. Hydrostatic pressure test > 10,000 mmH₂O according to EN ISO 811.

Industrial care category B3



Certifications



Logo

The product is certified with maximum 0,0400m² logo area. This approved area must not be exceeded. Logo on, respectively, front or back of the product can constitute only a maximum of 50% of the total approved logo area in order to maintain the EN ISO 20471-certification. Note: The listed area is only a guide to how much space is available for logo placement. In order to maintain the product's hi-vis class according to EN ISO 20471, the instructions on logo size must be observed.

Logo placement:

- Workwear logo. Left breast. Max 6x7 cm/2.3x2.7 inches
- Workwear logo. Mid-back. Max 25x20 cm/9.8x7.8 inches
- Workwear logo. Horizontal on right sleeve. Max 10x5 cm/3.9x1.9 inches
- Workwear logo. Special placement. Contact to discuss further

- Durable CORDURA®-reinforcement at the wrist to extend product life.
- Reinforcements inside the jacket, so the lining does not tear when you have tools in the trouser pockets
- Breathable, wind and waterproof with taped seams.
- Waterproof extension at the back that can be folded down in the rain and cold.
- Mesh with ventilation under the sleeves - opens with zip.

Technical info

Fluorescent and with vertical and oblique, transverse reflective strips. Two-toned. Breathable, wind and waterproof. Taped seams. Lining in mesh material. Detachable lined hood can be adjusted to fit over a helmet via drawstring. Adjustable wire on both sides of the hood. Mesh with ventilation under sleeves - opens with zip. High collar. Ribbed inner collar. Waterproof pen pocket on the sleeve. Fastening with zip and storm flap with press studs. Zipped inner pockets under storm flap - one designed especially for a mobile with holes for headset wire and guide loops to keep wire accessible. Zipped pocket under storm flap large enough to hold a 7-inch tablet. Flap on back of jacket can be folded up for standard back length or released for extended back. Chest pocket with zip. D-ring. Ergonomically shaped sleeves allow for high freedom of movement. Ribbed inner waistband to keep the cold out. CORDURA® fabric reinforced cuffs with press stud fastening. Front pockets with zip.

User

