

Datasheet

Stock No: 383-715

# RS Pro 3 Core Unscreened Grey PVC Industrial Cable, 250 V



## Product Details

Core construction 7 x 0.25 mm (0.34 mm<sup>2</sup>)

Unshielded LiYY

Fine-strand copper wire with PVC insulation

Colour and strand coding in accordance with DIN 47100

Cores stranded in layers

PVC outer sheath, grey (RAL 7000)

Operating temperature -5°C to +80°C

## Specifications

Number of Cores	3
Cross Sectional Area	0.34 mm <sup>2</sup>
Screened/Unscreened	Unscreened
Length	100m
Outer Diameter	4.9mm
Sheath Colour	Grey
Core Strands	7/0.25 mm
American Wire Gauge	22 AWG
Voltage Rating	250 V
Sheath Material	Polyvinyl Chloride PVC
Number of Strands	7
Insulation Material	PVC
Minimum Operating Temperature	-5°C
Maximum Operating Temperature	+70°C
Conductor Material	Copper
Minimum Bend Radius	10 x D
Cable Shape	Multicore
Conductor Resistance	55 Ω/km
Size of Strands	0.25 mm