

### Main

Range	Odace
Product or component type	Reading lamp
Device application	Reading USB charger
Device mounting	Flush
Device presentation	Mechanism with fixing frame
Switch function	Dimmer
Switch application	On/off switching
Colour tint	Aluminium
Market segment	Hotel

### Complementary

Type of USB power supply	USB type A
Actuator	Push-button
Rated lamp wattage	2 W
[Ue] rated operational voltage	240 V
Bulb base	Integral LED
Bulb type	LED
Control type	Touch type
Luminous flux	100 lm
Integrated connection type	USB port
Output current	2.1 A
Fixing mode	Screws
Shape of screw head	Pozidriv No 1
Clamping connection capacity	2.5 mm <sup>2</sup> for flexible cable(s) 2.5 mm <sup>2</sup> for rigid cable(s)
Height	71 mm
Width	71 mm
Depth	45 mm

### Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins