



MEGA S 125-PP1

Bolt-On Fuse, Small, 125A

Product Properties:

Explosion-proof	No
Release characteristic	Time-lag (T)
Rated voltage	32 V
Optical defect indication	Yes
Type of current	DC
Colour code	Black
Nominal voltage DC	32 V
Max. continuous voltage DC	32 V
Number of fuses	1 .
Model	Other
Max. current (I _{max})	125 A
Nominal current	125 A
Fuse type	Mega S

Dimensions:

Width	40.8 mm
MOQ	10 .
Unit	pck
Rated voltage	32 V
Mounting holes	M6
Centre-to-centre distance of connections	30 mm
Thickness	8.3 mm
Length	12.1 mm

Approvals:

Compliance:

Conflict Minerals	Contain "Tin"
REACH	No SVHC (Latest. 04 Feb 2026)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable

Other information:

ETIM-Class	EC004122 - Strip fuse
ETIM-Release	DYNAMIC
Trademark	NECORE
Product Group	Bolt-on / Strip fuses - Pin-pac
Search Description	MIDI
Alternative SKU	MEGAS125-PP1

Logistic information:

Barcode	733117610354
Country of origin	JP
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	10 .
Stock code	MEGA S 125-PP1
Taric code	85361050
Unit	pck

*We reserve the right to make technical changes and disclaim any typographical errors.