

A146 - Cold 15 Nitrile Sandy 3/4 Dipped Glove

Collection: Thermal Protection Gloves

Range: Hand Protection

Materials: Polyester, Acrylic, Elastic

Dipping:

Inner Pack: 12

Outer Carton: 144

Product information

Twin liner traps in heat. A 3/4 nitrile sandy dipping offers greater protection to the fingers and improved liquid protection. Open back for breathability. 250°C Contact heat protection. A fantastic glove for a wide range of industries.

Thermal Protection Gloves

When cold thermal hazards are present, the hands' motor skills can be greatly reduced, this leads to increased risk of accidents and injury. Specially designed thermal protective gloves are available to combat these dangers in hazardous environments.

Hand Protection

A wide and increasing range of hand protection products is available. In order to help cater to every need. Only the best materials and manufacturing methods are used in the production of Portwest's extensive range of Hand Protection products....

Standards

EN ISO 21420: 2020 Dexterity 3
EN 388: 2016 + A1: 2018 (4242X)
EN 407: 2020 (X2XXXX)
EN 511: 2006 (X2X)
ANSI/ISEA 105: 2016 CUT Level (A2)
ANSI/ISEA 105: 2016 ABRASION Level (3)



Features

- 3/4 dipped for increased protection
- Twin liner traps in heat through increased insulation
- Provides contact heat protection up to 250°C for 15 seconds
- Flexible sandy nitrile coating offers great grip in wet and dry conditions
- Superb abrasion and tear resistance
- Specially designed for use in cold conditions
- 15 gauge liner provides the best balance of dexterity and durability
- OEKO-TEX® STANDARD 100 approved
- Breathable seamless liner
- CE certified
- Retail tag which aids presentation for retail sales



PRODUCT SPECIFICATION & TECHNICAL DATASHEET

A146 - Cold 15 Nitrile Sandy 3/4 Dipped Glove

Commodity Code: 6116102091

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)

Bracetown Business Park

D15 YN2P, Ireland

Cert No: 2777/26715-01/E00-00

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
A146BKRL	Black	60.0	43.0	40.0	0.0890	0.1032	5036108199334	15036108685100
A146BKRXL	Black	60.0	43.0	40.0	0.0980	0.1032	5036108199341	15036108685117
A146BKRXXL	Black	60.0	43.0	40.0	0.1140	0.1032	5036108199358	15036108685124