



120-240V, 50WATTS CS060, 06000.0-00,

Model		
product brand name	SIVACON	
product designation	heater unit	
design of the product	Semiconductor	
General technical data		
consumed active power rated value	50 W	
Voltage		
type of voltage of the operating voltage	AC/DC	
continuous heating power at 20 °C	50 W	
operating voltage		
<ul style="list-style-type: none"> rated value minimum rated value maximum at AC at 50 Hz rated value minimum at AC at 50 Hz rated value maximum at AC at 60 Hz rated value minimum at AC at 60 Hz rated value maximum at DC rated value minimum at DC rated value maximum 	<ul style="list-style-type: none"> 120 V 240 V 120 V 240 V 120 V 240 V 120 V 240 V 	
Protection class		
protection class IP	IP20	
Product details		
product component		
<ul style="list-style-type: none"> blower thermostat 	<ul style="list-style-type: none"> No No 	
Mechanical Design		
height	110 mm	
width	60 mm	
depth	90 mm	
Approvals Certificates		
General Product Approval	other	Environment



EG-Konf.



UR



[Confirmation](#)

[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR2131-4A>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR2131-4A>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR2131-4A

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

5/24/2025 

