

D3PC-MP 0.20-0.50-F-SN-L - Crimp contact



1340361

<https://www.phoenixcontact.com/gb/products/1340361>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, nominal current: 6 A, contact surface: Tin

Commercial data

Item number	1340361
Packing unit	200 pc
Minimum order quantity	200 pc
Sales key	AABCUB
Product key	AABCUB
GTIN	4063151646462
Weight per piece (including packing)	0.442 g
Weight per piece (excluding packing)	0.474 g
Customs tariff number	85366990
Country of origin	CN

D3PC-MP 0.20-0.50-F-SN-L - Crimp contact



1340361

<https://www.phoenixcontact.com/gb/products/1340361>

Technical data

Product properties

Product type	Crimp contact
Product family	D3PC-MP-F

Connection data

Stripping length	4.5 mm
Conductor cross section AWG	24 ... 20

Material specifications

Contact surface	Tin Sn
Contact surface material	Tin
Metal surface terminal point (top layer)	Tin (1 - 3 µm Sn)
Metal surface contact area (top layer)	Tin (1 - 3 µm Sn)
Surface characteristics	hot-dip tin-plated
Contact material	Cu alloy

Electrical properties

Nominal current I_N	6 A
-----------------------	-----

D3PC-MP 0.20-0.50-F-SN-L - Crimp contact



1340361

<https://www.phoenixcontact.com/gb/products/1340361>

Classifications

ECLASS

ECLASS-13.0	27460291
-------------	----------

ETIM

ETIM 9.0	EC002943
----------	----------

D3PC-MP 0.20-0.50-F-SN-L - Crimp contact



1340361
<https://www.phoenixcontact.com/gb/products/1340361>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk