



Product data sheet

Power tools for trade & industry

Cordless Impact Drill/Drivers

PRO GSB 18V-65



The compact, robust impact drill for tough screwdriving applications

The most important data

Torque (soft/hard/max.)	-/-/76 Nm
No-load speed (1st gear / 2nd gear)	0 – 550 / 0 – 2,100 rpm
Battery voltage	18.0 V

Part Number 0 615 A50 08J

Technical data

Technical data

Torque (soft/hard/max.)	-/-/76 Nm
No-load speed (1st gear / 2nd gear)	0 – 550 / 0 – 2,100 rpm
Battery type	Lithium-Ion
Max. impact rate	27,000 bpm
Chuck capacity, min./max.	1.5 / 13 mm
Battery voltage	18.0 V
Weight excl. battery	1.12 kg
Torque settings	20
Packaging dimensions (width x length x height)	390 x 440 x 112 mm
Chuck type	13-mm keyless chuck
BITURBO	No
Work light	+
Tool design	Pistol

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Performs tough drilling applications with ease thanks to improved 65 Nm torque
- Compact and handy in tight spaces with a head length of only 175 mm
- Keeps you protected and in control with switchable KickBack Control
- Maximizes illumination coverage with dual working lights
- Powerful performance thanks to durable brushless motor and robust drive train

**HEAVY
DUTY****65/31
Nm****0-
27000
bpm****METAL CHUCK
1.5-13 mm****BRUSHLESS
MOTOR****ON OFF
KICKBACK
CONTROL****2 x LED LIGHT****PROFESSIONAL
18V
SYSTEM**

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

