

8094SL
Lifting chain slings, 4 legs, self-locking hook, grade 8

CE

EN 818-4

TECHNICAL DATA

- safety factor: 4
- chain-sling identification tag

ATTACHED CERTIFICATES

- Manufacturer's Certificate UNI EN818-4
- CE Declaration of Conformity

AVAILABLE CERTIFICATES

- Technical product specifications



	art.	 D mm	L m	WLL ton
080940201	8094SL D6-1	6*	1	2,36
080940202	8094SL D6-2	6*	2	2,36
080940203	8094SL D6-3	6*	3	2,36
080940204	8094SL D6-4	6*	4	2,36
080940221	8094SL D7-1	7*	1	3,15
080940222	8094SL D7-2	7*	2	3,15
080940223	8094SL D7-3	7*	3	3,15
080940224	8094SL D7-4	7*	4	3,15
080940241	8094SL D8-1	8*	1	4,25
080940242	8094SL D8-2	8*	2	4,25
080940243	8094SL D8-3	8*	3	4,25
080940244	8094SL D8-4	8	4	4,25
080940251	8094SL D10-1	10*	1	6,7
080940252	8094SL D10-2	10	2	6,7
080940253	8094SL D10-3	10	3	6,7
080940254	8094SL D10-4	10	4	6,7
080940331	8094SL D13-1	13	1	11,2
080940332	8094SL D13-2	13	2	11,2
080940333	8094SL D13-3	13	3	11,2
080940334	8094SL D13-4	13	4	11,2
080940361	8094SL D16-1	16	1	17
080940362	8094SL D16-2	16	2	17
080940363	8094SL D16-3	16	3	17
080940364	8094SL D16-4	16	4	17
080940402	8094SL D20-2	20	2	26,5
080940403	8094SL D20-3	20	3	26,5
080940404	8094SL D20-4	20	4	26,5