



### **Datasheet**

# RS PRO Straight Plug Male 4 pin Solder Brass OD 4.2-5.2mm

Stock No: 209-5661



RS Pro's range of Chrome plated Brass push-pull locking connectors offer exceptional quality that is found in many cutting-edge connectors, including full 360° EMC shielding and high mating life. As has become standard within the RS Pro brand you can expect high quality products but at a reasonable price. These connectors are ideal for use in medical devices, testing equipment, audio equipment and other high-end indoor applications.

## **Features & Benefits:**

- Push-pull latching system
- Chrome plated Brass
- IP50
- 360° Screening for full EMC shielding
- 7A Current Rating

#### **Technical**

| Characteristics           | Value Standard                    |                      |  |
|---------------------------|-----------------------------------|----------------------|--|
| Endurance                 | >5000cycles                       | IEC60512-5test9a     |  |
| Humidity                  | Up to 95% at 60°C                 |                      |  |
| Temperature range         | -55°C, +250°C                     |                      |  |
| Resistance to vibration   | 10-2000Hz,15g IEC 60512-4 test 6d |                      |  |
| Shock resistance          | 100g, 6ms                         | IEC 60512-4 test 6c  |  |
| Salt spray corrosion test | >96hrs                            | IEC 60512-6 test 11f |  |
| Protection index (mated)  | IP50                              | IEC 60529            |  |
| Climatical category       | 55/175/21                         | IEC 60068-1          |  |


#### **Electrical**

| Characteristics |          | Value  | Standard      |
|-----------------|----------|--------|---------------|
| Shielding       | at 10MHZ | >75 dB | IEC 60619-1-3 |
| efficiency      | at 1GHZ  | >40 dB | IEC 60619-1-3 |





# **Dimensional line drawings**



CONNECTOR SOLDER CUP VIEW

















7(\$0,5)

**Quality Standards** 







