



Frame paneling IP30, W: 1100 mm

Model	
product brand name	SIVACON S4
product designation	rack cladding
Protection class	
protection class IP	IP30
suitability for use for outside use	No
Appearance	
color	light grey
Mechanical Design	
height	1 975 mm
width	1 100 mm
depth	25 mm
installation location	in the field
net weight	5 380 g
material	sheet-steel
Approvals Certificates	
General Product Approval	other



[Miscellaneous](#)



[Confirmation](#)

Environment

[Environmental Con-
firmations](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/109813875>
Information- and Downloadcenter (Catalogs, Brochures,...)
<http://www.siemens.com/lowvoltage/catalogs>
Industry Mall (Online ordering system)
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ2197-0BA13>
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
<https://support.industry.siemens.com/cs/ww/en/ps/8PQ2197-0BA13>
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)
http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ2197-0BA13
CAx-Online-Generator

last modified: 5/24/2025 

