

特点

- 导线绞线是柔性的，
- 耐油，温度高达 60°C
- 英国制造
- 各种护套颜色
- 适用于布线电路

RS PRO 棕色三级电缆， 1mm² CSA ， 1kV 直流， 600V 交 流， 17A ， 100 米

RS 库存号： 180-5933



RS 认证产品为您提供所有产品类别的专业品质部件。我们的产品系列经过工程师测试、提供与杰出品牌相当的质量、而无需支付高昂的价格。

商品描述属性 1

我们的 RS PRO 三级电缆设计用于电气设备，最常用于包括电源开关设备在内的布线项目。该电缆还特别适用于整流器设备，电动机启动器和控制器内的内部连接。我们的 RS PRO 三级电缆系列具有高 Durable 电线，由柔性铜制成，采用 HR PVC (耐热聚氯乙烯) 绝缘封装。最大工作温度高达 105°C，使其可用于各种应用，如电气机柜。RS PRO 三级电缆提供各种不同颜色的 HR PVC 护套，包括蓝色，黑色，红色，棕色，绿色，黄色等，可适应多种应用

一般规格

| | |
|------|---------------------------------------|
| 类型 | 三级 |
| 三级 | 是的 |
| 护套颜色 | 棕色 |
| 火灾行为 | 阻燃 |
| 应用 | 电气柜、工业电气安装、小型电子设备、继电器和仪表板、控制计量、电动机启动器 |

电气规格

| | |
|------|----------------|
| 额定电压 | 1kVdc 、 600Vac |
| 额定电流 | 17A |
| 导线材料 | 铜 |
| 绝缘材料 | pvc |

机械规格

| | |
|------|------------------|
| 长度 | 100m |
| 横截面积 | 1mm ² |
| 外径 | 3mm |
| 芯线束 | 32/0.2mm |
| 绞线尺寸 | 0.2mm |
| 重量 | 18kg/km |

操作环境规格

| | |
|--------|--------|
| 最高工作温度 | 105°C |
| 最大导体温度 | 60°C 油 |

认证

| | |
|----------|-------------------------------|
| 合规性 / 认证 | csa、ul、bsi、rohs 合规性认证。BSI EEE |
| 符合标准 | BS6231 |



| | | |
|----------------------|-----------------|--|
| Stock number: | 180-5936 | Black tri-rated cable 1.0mm 100m |
| | 180-5941 | Blue tri-rated cable 1.0mm 100m |
| | 180-5933 | Brown tri-rated cable 1.0mm 100m |
| | 180-5970 | Green tri-rated cable 1.0mm 100m |
| | 180-5934 | Green/yellow tri-rated cable 1.0mm 100m |
| | 180-5942 | Grey tri-rated cable 1.0mm 100m |
| | 180-5940 | Orange tri-rated cable 1.0mm 100m |
| | 180-5944 | Pink Tri-rated cable 1mm 100m |
| | 180-5938 | Red tri-rated cable 1.0mm 100m |
| | 180-5943 | Violet tri-rated cable 1.0mm 100m |
| | 180-5937 | White tri-rated cable 1.0mm 100m |
| | 180-5939 | Yellow tri-rated cable 1.0mm 100m |