

Component Labels for Mini-Com® Classic Series Faceplates with Label and Label Cover



Suggested Label Solutions for TIA/EIA-606-A Compliance

Faceplate Part Number	Laser/Ink Jet Desktop Printer Label	TDP43ME Thermal Transfer Desktop Printer Label	PanTher™ LS8E Hand-Held Printer Label	Cougar™ LS9 Hand-Held Printer Label
All CFPL Parts	C195X040Y1J	C195X040Y1T	C195X040Y1C	T038X000FJC-BK‡

For complete labeling solutions and product information, reference charts on pages O.1 – O.22.
‡For non-adhesive labeling solution, do not remove liner from label.



Mini-Com® Classic Series Sloped Faceplates with Label and Label Cover

- Accept Mini-Com® Modules for STP and UTP, fiber optic, and audio/video, which snap in and out for easy moves, adds, and changes
- Include label/label covers for easy port identification
- Replacement label/label covers available
- Optional icons available



CFPSL2IWY



CFPSL4IWY



CFPSL6IWY



CFPHSL4IW

Part Number	Part Description	Color‡	Std. Pkg. Qty.	Std. Ctn. Qty.
CFPSL2IWY	Single gang, sloped vertical faceplate accepts two Mini-Com® Modules.	Off White	1	10
CFPSL4IWY	Single gang, sloped vertical faceplate accepts four Mini-Com® Modules.	Off White	1	10
CFPSL6IWY	Single gang, sloped vertical faceplate accepts six Mini-Com® Modules. Requires minimum 1.9" wide electrical box for proper mounting.	Off White	1	10
CFPHSL4IW	Single gang, sloped horizontal faceplate accepts four Mini-Com® Modules.	Off White	1	10

‡For other colors replace suffix IW (Off White) with EI (Electric Ivory), WH (White), or IG (International Gray). All faceplates supplied with mounting screws.

Component Labels for Mini-Com® Classic Series Sloped Faceplates with Label and Label Cover



Suggested Label Solutions for TIA/EIA-606-A Compliance

Faceplate Part Number	Laser/Ink Jet Desktop Printer Label	TDP43ME Thermal Transfer Desktop Printer Label	PanTher™ LS8E Hand-Held Printer Label	Cougar™ LS9 Hand-Held Printer Label
All CFPSL Parts	C195X040Y1J	C195X040Y1T	C195X040Y1C	T038X000FJC-BK‡
All CFPHSL4 Parts	C261X035Y1J	C261X035Y1T	C261X035Y1C	T038X000FJC-BK‡

For complete labeling solutions and product information, reference charts on pages O.1 – O.22 of SA-NCCB51.
‡For non-adhesive labeling solution, do not remove liner from label.