

Features

- Lightweight and flexible
- Length 25m
- EN ISO 3821/EN 559

RS PRO Hose Pipe

RS Stock No.: 146-7755, 146-7756, 146-7758,
146-7759



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Lightweight, flexible twin hose for oxygen and acetylene, designed for use with mobile and stationary autogenic welding equipment. Dividing

groove allows easy separation and simple fitting to a gas cylinder or welding gun. Also ideal for other purposes, e.g. air inlet/outlet on sandblasting equipment.

Normally installed using brass fittings, either with hose clamps or crimp-on fittings.

General Specification

Brand	RS PRO
Features	Flexible
Materials	EPDM, SBR
Colour	Red & Blue
Length	25m
Suitable Applications	Gas
Maximum Operating Temperature	+80°C
Minimum Operating Temperature	-30°C
Hose Pipe Action	Transfer
Bend Radius	45mm
Standards Met	EN ISO 3821/EN 559

Products in series

Stock No.	Lenght	Inner Diameter	Outer Diameter	Colour
146-7755	25m	5mm	11,4mm	Red & Blue
146-7756	25m	6,3mm	13,5mm	Red & Blue
146-7758	25m	8mm	15,2mm	Red & Blue
146-7759	25m	9,5mm	16,7mm	Red & Blue