


Technical data sheet

Article number:
112-52104

CTT60R



Product Group	Cable ties for hose and gaiter
Product Family	CTT-Series natural and black
Material	Polyamide 6.6 (PA66)
Colour	Natural (NA)
Application Range	Indoor Use
Application Tool	MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7SP, EVO7i, EVO7iSP
Bundle Ø max.	45.0 mm
Bundle Ø min.	1.5 mm
Flammability	UL 94 V2
Length (L)	203.2 mm
Min.Tensile Strength	267 N
Operating Temperature	-40 °C to +85 °C
Package Content packed in	pack
Pack Cont.	100 pcs.
Releasable Closure (Yes/No)	No
Specifications	UL
Thickness (T)	1.2 mm
Toothing (Serration)	Inside Serrated
UL-File Number	E64139
Variant	Inside Serrated
Weight/Unit	0.0014 kg
Width (W)	4.7 mm

