



ENGLISH

Datasheet

## RS Pro Patton Electronics SHDSL RJ45 Wired Modem, 10/100Mbit/s, 5 x 4.7 x 1.52in

RS Stock No: **624-6230**



### Product Details

RS Pro SHDSL modem has RJ45 LAN port with a speed of 10/100 Mbit/s. It measures 5 x 4.7 x 1.52 Inch. The model 3088 G.SHDSL rocket link-G NTU is the perfect choice for users or service providers who need high speed dedicated network connections and know what interface they want. Based on the ITU and ETSI G.SHDSL G.991.2 standard, the rocket link-G NTUs enable the providers to extend their reach-and-range by delivering rate-adaptive n x 64 symmetrical speeds from 192 kbps to 4.6 Mbps all over a single pair of wires. The front panel LEDs provides users with quick feedback on unit operation.

### Features and Benefits

- nx64 rates to 4.6 Mbps
- Low cost fixed interfaces
- Netlink plug and play
- Supplied with CD manual, power supply, power cord; DB9 cable



**Specifications:**

Depth	4.7 in
Dimensions	5 x 4.7 x 1.52 in
Height	1.52 in
LAN Port Speed	10/100 Mbit/s
LAN Port	RJ45
Modem Type	SHDSL
Weight	720 g
Width	5 in