



Main

Range of product	Spacial CRN
Application	Multi-purpose
Category	Compact enclosure
Enclosure nominal height	600 mm
Enclosure nominal width	500 mm
Enclosure nominal depth	250 mm
Installation accessory type	Wall-mounting
Device composition	Body 1 Cable gland plate 1 Door 1 Lock 1
Door type	Plain
Mounting plate description	Without mounting plate

Complementary

Body type	Sides made from a single folded section Back welded with double profile forming a protected sealed area
Number of doors	1 front face
Door opening	Reversible 120 °
Lock type	3 mm double-bar lock
Type of gland plate	Standard
Accessibility for operation	Front
Removable parts	Door by hinges Cable gland plate by screws
Material	Steel for body
Surface finish	Epoxy-polyester powder
Colour	Grey RAL 7035
Standards	IEC 62208
Product certifications	CUL UL

Environment

IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
RoHS EUR status	Compliant
RoHS EUR conformity date	0940