



Main

Range of product	TeSys fuse-disconnector
Product or component type	Fuse-disconnector
Device short name	LS1 D
Poles description	3P

Complementary

Mounting support	Rail
Mounting position	Vertical +/- 23°
Control type	Toggle
[Ue] rated operational voltage	60 V for signalling circuit 250 V for signalling circuit 690 V for power circuit
[Ie] rated operational current	32 A for power circuit 6 A for signalling circuit
Fuse size	10 x 38 mm
Fuse type	AM GG
Connections - terminals	2 flexible cable(s) 1.5...4 mm ² without cable end on spring terminals for power circuit 2 solid cable(s) 1...4 mm ² on spring terminals for power circuit

Environment

Standards	IEC 60947-3
Product certifications	BV UR
Protective treatment	TH
Ambient air temperature for operation	-50...70 °C
Height	89 mm
Width	45 mm
Depth	68.3 mm
Product weight	0.27 kg

Contractual warranty

Period	18 months
--------	-----------