

ENGLISH

Datasheet

Stock No: 113-4312

Indicator, 8mm Panel Mount, Recessed, Green LED, Lead Pins Termination, 5 mm Lamp Size, 3.1 V



Image representative of range

Product Details

LEDs with metal support, 34 type, board hole 8 mm

Brought to you under the trusted RS Brand, this LED indicator features a recessed lens behind a prominent bezel that not only protects the lens but offers a sixty degree angle of diffusion. Equipped with lead pins, this panel mounted indicator is easy to install, and has a robust nickel plated brass body.

- LED indicators for panel mounting.
- . The support is equipped with a standard 5 mm LED.
- · Supplied with nuts and washers.





Specifications

Voltage Rating	3.1 V
Light Output Colour	Green
Mounting Hole Size	8mm
Lamp Size	5 mm
Length	17 mm
Туре	Panel Mount
Lamp Type	LED
Termination Type	Lead Pins
Bezel Style	Recessed
Bezel Colour	Chrome
Intensity	1.8 mcd
Current Rating	20 mA