

## VPS210-R Voltage Probe Set, 200 MHz, Red (one, red)



**Double insulated voltage probe for ScopeMeter 190 series.**

**Each probe set includes:**

- 600 V CAT III / 1000 V CAT II rated 10:1 Voltage Probe
- Hook Clip for Probe Tip
- Ground Lead with Mini Alligator
- Insulation Sleeve
- 30 V CAT II rated Ground Spring for Probe Tip

**Specification:**

- Attenuation: 10x
- Bandwidth: 200 MHz
- Max. Input Voltage: 1000 V CAT II or 600 V CAT III
- Max. Voltage to ground: 1000 V CAT II or 600 V CAT III per IEC / EN61010-031
- Input Resistance: 10 M $\Omega$
- Input Capacitance: 12 pF
- Compensation range: 10 to 22 pF
- Cable Length: 1.2 m