




0401 - BALL VALVE MALE FEMALE



maximum working pressure	40 bar 4 MPa 580 psi
working temperature	-20 to 80 °C -4 to 176 °F 253 to 353 °K
body	NICKEL PLATED BRASS
retaining nut	NICKEL PLATED BRASS
stem	BRASS
stem seal	NBR
'O'-rings	NBR
ball seal	NBR
handle	ZAMAK

Part Nb	C	E (mm)	E1 (mm)	F (mm)	H (mm)	H1 (mm)	J (mm)	L (mm)	L1 (mm)	M (mm)	 (kg)
	All	All	All	All	All	All	All	All	All	All	All
0401 04 10	G1/8	8	7	14	35	29	14	45	25	48	.094
0401 05 10	G1/8	8	7	19	38	31	19	51	27	48	.16
0401 07 13	G1/4	12	9	19	38	31	19	52	28	48	.15
0401 10 17	G3/8	12	11	24	45	43	24	58	31	69	.234
0401 13 21	G1/2	15	12	27	47	44	27	66	34	69	.286
0401 18 27	G3/4	16.5	12	38	63	54	39	79	39	108	.652
0401 23 34	G1	19	15	46	67	57	48	91	47	108	.952
0401 32 42	G1 1/4	21.5	18	60	97	115	55	113	59	108	2.385