



### Main

Range of product	Acti 9
Product name	Acti 9 iERL
Product or component type	Extension for changeover relay
Device short name	IERL
Device application	Extension for changeover relay
Signal contacts composition	1 C/O + 1 NO
[Uc] control circuit voltage	230...240 V AC 50/60 Hz

### Complementary

[Ie] rated operational current	10 A at 230 V AC (cos Phi = 1)
[Ui] rated insulation voltage	250 V AC
Supply holding power	8 VA
Supply inrush power	8 VA
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	2
Height	88 mm
Width	18 mm
Depth	70 mm
Net weight	0.112 kg
Colour	White
Electrical durability	AC-21: 100000 cycles
Connections - terminals	Tunnel type terminals 0.5...6 mm <sup>2</sup> Connection by clip

### Environment

Standards	NF C 45-250 IEC 255
IP degree of protection	IP20
Ambient air temperature for operation	-5...55 °C
Ambient air temperature for storage	-40...70 °C

### Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### Contractual warranty

Warranty	18 months
----------	-----------