

Han1A CA 3+PE+Shld +latch m/- PVC 10m



Image is for illustration purposes only. Please refer to product description.

Part number	33 50 080 0202 100
Specification	Han1A CA 3+PE+Shld +latch m/- PVC 10m
HARTING eCatalogue	https://harting.com/33500800202100

Identification

Category	System cabling
Series	Han [®] 1A
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	Han [®] 1A Male
Type of cable	Copper cable (round)
Description of the cable	Oil resistant

Version

Cable length	10 m
Number of cores	4
Core structure	4x 1.5 mm ²
Shielding	Shielded
Number of contacts	3
PE contact	Yes
Locking type	Snap-in latches
Details	Not be coupled or decoupled under electrical load. Assembly and installation must be carried out by a qualified electrician.

Technical characteristics

Rated current	10 A
Rated voltage	400 V
Rated voltage conductor-earth	300 V



Pushing Performance
Since 1945

Technical characteristics

Limiting temperature	-30 ... +80 °C unmoved -10 ... +80 °C moved
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP65
Cable diameter	8.3 mm

Material properties

Material (cable)	PVC
Colour (cable)	Grey
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	567c8b78-5fa0-43aa-a4c0-beb9d99b7769
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

Specifications	IEC 60332-1-2 Flame retardancy
----------------	--------------------------------

Commercial data

Packaging size	1
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140237285
eCl@ss	27060311 Assembled sensor actuator-line
ETIM	EC001855
UNSPSC 24.0	26121604