




Precision Brand Stainless Steel Shim Stock

ENGLISH

	<p>PRECISION BRAND Stainless Steel Shim Stock is a full hard, cold rolled, Type 302</p> <p>Rockwell Hardness: C40-45</p> <p>Meets SAE-30302, AISI-T302, ASTM A-666</p> <p>Ultimate Tensile Strength: 185,000p.s.i. min</p> <p>Shim continuously marked along its length as follows:</p> <p>Shim Thickness</p> <p>Material</p> <p>Batch/Lot number</p> <p>Web address for trace ability record of Batch/Lot number</p>
--	---

RS Code	Manufacturers Code	Description	
		Stainless Steel Shim: Metric	
519-024	77-422-971	0.05mm	150mm x 1.25m
518-801	77-422-972	0.10mm	150mm x 1.25m
518-970	77-422-973	0.15mm	150mm x 1.25m
518-762	77-422-974	0.20mm	150mm x 1.25m
518-857	77-422-975	0.25mm	150mm x 1.25m
518-980	77-422-976	0.30mm	150mm x 1.25m
519-062	77-422-977	0.40mm	150mm x 1.25m
519-119	77-422-978	0.50mm	150mm x 1.25m
518-952	77-422-979	0.65mm	150mm x 1.25m
518-942	77-422-980	0.80mm	150mm x 1.25m
		Stainless Steel Shim: Inch	
519-074	77-422-125	0.001"	6" x 50"
519-096	77-422-150	0.002"	6" x 50"
519-090	77-422-175	0.003"	6" x 50"
518-829	77-422-220	0.005"	6" x 50"
518-873	77-422-285	0.008"	6" x 50"
657-1924	77-422-320	0.010"	6" x 50"
519-028	77-422-340	0.012"	6" x 50"
519-141	77-422-365	0.015"	6" x 50"
518-734	77-422-390	0.020"	6" x 50"
518-738	77-422-410	0.025"	6" x 50"
519-012	77-422-430	0.031"	6" x 50"
		Assortment Packs	
518-946	77-422-161	Stainless Steel Metric assorted pack: Sheets 150mm x 300mm	8 pce 0.05mm to 0.50mm
519-129	77-422-445	Stainless Steel Inch assorted pack: Sheets 6" x 12"	8 pce 0.001" to 0.020"

***Bold italic* Manufacturers codes indicate which sizes make up the contents of the assortment packs**