

Angular contact ball bearings 7311-B-XL-TVP (Series 73..-B)

main dimensions to DIN 628-1, contact angle $\alpha = 40^\circ$

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue selection system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

d	55 mm
D	120 mm
B	29 mm
a	51 mm
D ₁	95,3 mm
d ₁	80,3 mm
D _{a max}	109 mm
d _{a min}	66 mm
D _{b max}	114,4 mm
r _{1 min}	1 mm
r _{a1 max}	1 mm
r _{a max}	2 mm

r_{min}	2 mm	
α	40 °	Contact angle
m	1,38 kg	Mass
C_r	86000 N	Basic dynamic load rating, radial
C_{0r}	61000 N	Basic static load rating, radial
C_{ur}	4250 N	Fatigue limit load, radial
n_G	7000 1/min	Limiting speed
n_{9r}	5600 1/min	Reference speed



