



# Wiha SoftFinish® electric.

The safe and comfortable insulated VDE screwdriver.



slimTECHNOLOGY



The right tool at a glance, thanks to the printed screw symbol on the handle end.



Applications on live equipment are subject to very special requirements. The focus is on absolute user safety and Wiha demonstrates this with a wealth of details.

The high quality blade insulation is moulded directly onto the blade and therefore guarantees safety when working on live equipment up to 1500 V DC or 1000 V AC. To maintain this safety, each screwdriver of the SoftFinish® electric series is individually tested in a water bath at 10000 Volts according to IEC 60900:2004.

The roll-off protection and the special handle geometry offer optimum handling and electrical safety, even in critical applications.



**slimTECHNOLOGY:**  
Up to 33% reduction of the blade diameter in the critical working area allows effortless access to low-lying fastening / spring elements.



When working with VDE tools, observe the national safety and accident prevention regulations.



## Wiha SoftFinish® electric.

- Safety when working with live equipment up to 1000 V AC and 1500 V DC
- Each screwdriver is individually tested in a water bath at 10.000 Volts according to IEC 60900:2004
- Awarded the GS symbol for tested safety
- Multi-component SoftFinish® handle provides maximum user comfort

## Wiha SoftFinish® electric slimFix.

- Unlimited access
- Blades up to 33% narrower due to integrated insulation
- Actuating tool for spring clips (wedge-profiled output geometry)

### For slotted, Phillips and Pozidriv screws.



**NEW**  
**3201**

**SoftFinish® electric slimFix slotted screwdriver.**  
Insulation 1000 V AC, VDE-tested and with GS mark.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, black-finish.  
Protective insulation spray-coated directly onto the blade and completely integrated into the blade in the lower area.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Standards: DIN ISO 2380. Manufactured acc. to IEC 60900:2004.

Application: For all work on or around electrical components up to 1000 V AC.

Extra: The integrated protective insulation enables low-lying fastening and spring elements to be reached and manipulated.

Order-No.	⌀	↔	⊖	↔	↔	↔
35446 6	3.5	100	0.6	204	23	10
35390 2	4.0	100	0.8	211	30	10
35391 9	5.5	125	1.0	243	36	10
35392 6	6.5	150	1.2	268	36	10



**NEW**  
**3211**

**SoftFinish® electric slimFix Phillips screwdriver.**  
Insulation 1000 V AC, VDE-tested and with GS mark.

Blade: Protective insulation spray-coated directly onto the blade and completely integrated into the blade in the lower area.

Standards: DIN ISO 8764. Manufactured acc. to IEC 60900:2004.

Extra: The integrated protective insulation enables low-lying fastening and spring elements to be reached and manipulated.

Order-No.	⊕	↔	↔	↔	↔
35393 3	PH1	80	191	30	10
35394 0	PH2	100	218	36	10



**NEW**  
**324**

**SoftFinish® electric slimFix Pozidriv screwdriver.**  
Insulation 1000 V AC, VDE-tested and with GS mark.

Blade: Protective insulation spray-coated directly onto the blade and completely integrated into the blade in the lower area.

Standards: DIN ISO 8764. Manufactured acc. to IEC 60900:2004.

Extra: The integrated protective insulation enables low-lying fastening and spring elements to be reached and manipulated.

Order-No.	⊕	↔	↔	↔	↔
35395 7	PZ1	80	191	30	10
35396 4	PZ2	100	218	36	10

### For slotted, Phillips and Pozidriv screws.



**320N**

**SoftFinish® electric slotted screwdriver.**  
Insulation 1000 V AC, VDE-tested and with GS mark.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, black-finish.  
Insulation moulded directly onto blade.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Standards: DIN ISO 2380. Manufactured acc. to IEC 60900:2004.

Application: For all work on or around electrical components up to 1000 V AC.

Order-No.	⌀	↔	⊖	↔	↔	↔
00819 2	2.0	60	0.4	164	23	10
00820 8	2.5	75	0.4	179	23	10
00821 5	3.0	100	0.5	204	23	10
00822 2	3.5	100	0.6	204	23	10
00823 9	4.0	100	0.8	211	30	10
00824 6	4.5•	125	1.0	236	30	10
00825 3	4.5•	175	1.0	286	30	5
31863 5	4.5•	200	1.0	311	30	10
00826 0	5.5	125	1.0	243	36	10
00827 7	5.5•	175	1.0	293	36	5
00828 4	6.0•	150	1.2	268	36	10
00829 1	6.5	150	1.2	268	36	10
00830 7	8.0	175	1.2	299	41	10
00831 4	8.0	175	1.6	299	41	10
00832 1	10.0	200	1.6	324	41	10

• Additional dimension. Non-DIN size



**321N**

**SoftFinish® electric Phillips screwdriver.**  
Insulation 1000 V AC, VDE-tested and with GS mark.

Standards: DIN ISO 8764. Manufactured acc. to IEC 60900:2004.

Order-No.	⊕	↔	↔	↔	↔
00846 8	PH0	60	164	23	10
00847 5	PH1	80	191	30	10
00848 2	PH2	100	218	36	10
00849 9	PH3	150	268	41	10
00850 5	PH4	200	318	41	5



**324**

**SoftFinish® electric Pozidriv screwdriver.**  
Insulation 1000 V AC, VDE-tested and with GS mark.

Standards: DIN ISO 8764. Manufactured acc. to IEC 60900:2004.

Order-No.	⊕	↔	↔	↔	↔
00877 2	PZ0	60	164	23	10
00878 9	PZ1	80	191	30	10
00879 6	PZ2	100	218	36	10
00880 2	PZ3	150	324	41	5

Products on this page are VDE-tested



# Wiha SoftFinish® electric.

The safe and comfortable insulated VDE screwdriver.

## For Pozidriv screws.



AC 1000V  
IEC 60900:2004

**325** SoftFinish® electric TORX® screwdriver.  
Insulation 1000 V AC, VDE-tested and with GS mark.  
Blade: High quality chrome-vanadium-molybdenum steel, through hardened, black-finish.  
Insulation moulded directly onto blade.  
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.  
Standards: Manufactured acc. to IEC 60900:2004.  
Application: For all work on or around electrical components up to 1000 V AC.

Order-No.	Symbol	Size	Length	Width	Weight
03760 4	T5	60	164	23	10
03761 1	T6	60	164	23	10
03762 8	T7	60	164	23	10
00881 9	T8	60	164	23	10
00882 6	T9	60	164	23	10
00883 3	T10	60	164	23	10
00884 0	T15	80	191	30	10
00885 7	T20	80	191	30	10
00886 4	T25	80	198	36	10
00887 1	T27	100	218	36	10
00888 8	T30	100	218	36	10
00889 5	T40	150	274	41	5
03763 5	T45	150	274	41	5

## For Allen screws and internal square-drive screws.



AC 1000V  
IEC 60900:2004

**323N** SoftFinish® electric hex screwdriver.  
Insulation 1000 V AC, VDE-tested and with GS mark.  
Blade: Chrome-vanadium steel, through hardened, black-finish.  
Insulation moulded directly onto blade.  
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.  
Standards: Manufactured acc. to IEC 60900:2004.  
Application: For internal hex screws.

Order-No.	Symbol	Size	Length	Width	Weight
30361 7	2.5	75	179	23	10
30362 4	3.0	75	179	23	10
30363 1	4.0	75	186	30	10
30364 8	5.0	75	186	30	10
30365 5	6.0	100	218	36	10
30366 2	8.0	100	218	36	10



AC 1000V  
IEC 60900:2004

**358N** SoftFinish® electric square-drive (Robertson) screwdriver.  
Insulation 1000 V AC, VDE-tested and with GS mark.  
Blade: High quality chrome-vanadium-molybdenum steel, through hardened, black-finish.  
Insulation moulded directly onto blade.  
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.  
Standards: Manufactured acc. to IEC 60900:2004.  
Application: For fastening and unfastening internal square-drive (Robertson) screws.

Order-No.	Symbol	Size	Length	Width	Weight	
32396 7	Robertson 1	2.3	100	211	30	10
32397 4	Robertson 2	2.8	150	268	36	10

## For hex nuts.



AC 1000V  
IEC 60900:2004

**322** SoftFinish® electric hex nut driver.  
Insulation 1000 V AC, VDE-tested and with GS mark.  
Blade: Chrome-vanadium steel, through hardened, black-finish.  
Insulation moulded directly onto blade.  
Deep drawn socket.  
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.  
Standards: DIN 3125. Manufactured acc. to IEC 60900:2004.  
Application: For external hex screws and hex nuts.

Order-No.	Symbol	Size	Length	Width	Weight	
00853 6	4	125	236	30	10.2	10
00855 0	5	125	236	30	11.2	10
00856 7	5.5	125	236	30	11.2	10
00857 4	6	125	236	30	12.2	10
00858 1	7	125	243	36	14.5	10
00859 8	8	125	243	36	15.2	10
00860 4	9	125	243	36	16.0	10
00861 1	10	125	243	36	17.2	10
00862 8	11	125	243	41	19.2	5
00863 5	12	125	243	41	20.2	5
00864 2	13	125	243	41	22.2	5
00865 9	14	125	243	41	23.2	5
00866 6	15	125	243	41	25.2	5
00867 3	16	125	243	41	25.2	5
00868 0	17	125	243	41	27.2	5

## For hex nuts and hex socket screws.



AC 1000V  
IEC 60900:2004

**334N** VDE T-handle hex screwdriver.  
Insulation 1000 V AC, VDE-tested and with GS mark.  
Blade: Chrome-vanadium steel, through hardened, black-finish.  
Insulation moulded directly onto blade.  
Handle: VDE-insulated T-handle.  
Standards: Manufactured acc. to IEC 60900:2004.  
Application: For internal hex screws.

Order-No.	Symbol	Size	Length	Width	Weight	
27928 8	4	150	176	80	26	5
27929 5	5	150	182	100	32	5
27930 1	6	150	182	100	32	5
27931 8	8	150	182	100	32	5



AC 1000V  
IEC 60900:2004

**336N** VDE T-handle hex nut driver.  
Insulation 1000 V AC, VDE-tested and with GS mark.  
Blade: Chrome-vanadium steel, through hardened, black-finish.  
Insulation moulded directly onto blade.  
Deep drawn socket.  
Handle: VDE-insulated T-handle.  
Standards: Manufactured acc. to IEC 60900:2004.  
Application: For external hex screws and hex nuts.

Order-No.	Symbol	Size	Length	Width	Weight	
27932 5	8	200	232	100	32	5
27933 2	10	230	262	100	32	5
27934 9	13	230	262	100	32	5
27935 6	17	230	268	120	38	5





# Wiha SoftFinish® electric.

The safe and comfortable insulated VDE screwdriver.

## Slotted/Phillips set.



AC 1000V  
IEC 60900:2004

**NEW**  
**3201 K6** SoftFinish® electric slimFix slotted/ Phillips screwdriver set, 6 pcs.  
Insulation 1000 V AC, VDE-tested and with GS mark.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, black-finish.  
Protective insulation spray-coated directly onto the blade and completely integrated into the blade in the lower area.  
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.  
Standards: Manufactured acc. to IEC 60900:2004.  
Application: For all work on or around electrical components up to 1000 V AC.  
Extra: The integrated protective insulation enables low-lying fastening and spring elements to be reached and manipulated.

Order-No.	Series					
35389 6	3201 K6					1
⓪	3201	3.5x100	4.0x100	5.5x125	6.5x150	
⊕	3211	PH1x80	PH2x100			

## Slotted/Phillips and slotted/Pozidriv sets.



AC 1000V  
IEC 60900:2004

**320N K6** SoftFinish® electric slotted/ Phillips screwdriver set, 6 pcs.  
Insulation 1000 V AC, VDE-tested and with GS mark.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, black-finish.  
Insulation moulded directly onto blade.  
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.  
Standards: Manufactured acc. to IEC 60900:2004.  
Application: For all work on or around electrical components up to 1000 V AC.

Order-No.	Series					
00833 8	320N K6					1
⓪	320N	3.0x100	4.0x100	5.5x125	6.5x150	
⊕	321N	PH1x80	PH2x100			



AC 1000V  
IEC 60900:2004

**320N ZK6 S0** SoftFinish® electric slotted/ Pozidriv screwdriver set, 6 pcs.  
Insulation 1000 V AC, VDE-tested and with GS mark.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, black-finish.  
Insulation moulded directly onto blade.  
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.  
Standards: Manufactured acc. to IEC 60900:2004.  
Application: For all work on or around electrical components up to 1000 V AC.

Order-No.	Series					
25477 3	320N ZK6 S0					1
⓪	320N	2.5x75	3.5x100	4.5x125	5.5x125	
⊕	324	PZ1x80	PZ2x100			

Products on this page are VDE-tested

## Slotted/Phillips set.



AC 1000V  
IEC 60900:2004

**320N K7** SoftFinish® electric slotted/ Phillips screwdriver set, 7 pcs.  
Insulation 1000 V AC, VDE-tested and with GS mark.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, black-finish.  
Insulation moulded directly onto blade.  
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.  
Standards: Manufactured acc. to IEC 60900:2004.  
Application: For all work on or around electrical components up to 1000 V AC.

Order-No.	Series					
00834 5	320N K7					1
⓪	320N	2.5x75	4.0x100	5.5x125	6.5x150	
⊕	321N	PH1x80	PH2x100			
⓪	255-11	3.0x65				

Products on this page are VDE-tested

## TORX® and nut driver set.



AC 1000V  
IEC 60900:2004

**325N K6 01** SoftFinish® electric TORX® screwdriver set, 6 pcs.  
Insulation 1000 V AC, VDE-tested and with GS mark.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, black-finish.  
Insulation moulded directly onto blade.  
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.  
Standards: Manufactured acc. to IEC 60900:2004.  
Application: For all work on or around electrical components up to 1000 V AC.

Order-No.	Series				
29465 6	325N K6 01				1
⊙	325	T8x60	T9x60	T10x60	
		T15x80	T20x80	T25x80	



AC 1000V  
IEC 60900:2004

**322 K5** SoftFinish® electric hex nut driver set, 5 pcs.  
Insulation 1000 V AC, VDE-tested and with GS mark.

Blade: Chrome-vanadium steel, through hardened, black-finish.  
Insulation moulded directly onto blade.  
Deep drawn socket.  
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.  
Standards: Manufactured acc. to IEC 60900:2004.  
Application: For all work on or around electrical components up to 1000 V AC.

Order-No.	Series				
29466 3	322 K5				1
⊙	322	5.5x125	7x125	8x125	
		10x125	13x125		

Products on this page are VDE-tested