

Article data sheet



PREMIUM PLUS mobile multiboard grey feltboard

- High-quality mobile whiteboard, pinboard and flipchart
- One side: scratch-resistant magnetic enamel steel board surface suitable for writing on with dry erase whiteboard markers
- One side: pinboard with felt surface
- Matte coated aluminium board frame
- Footings and legs in matte coated steel
- Included: 4 lockable castors, 2 click-on paper hooks
- Height of the total product: 195 cm
- Board size: H 120 x W 76 cm

Highlights


- Ideal for individual work, small groups and flexible workspaces
- Perfect for diverse environments, from corporate offices and hotels to creative co-working spaces and production areas
- Supports structured collaboration, brainstorming and prioritization
- Space-saving all-in-one solution: whiteboard, pinboard and flipchart
- Click-on paper hooks included for flexible flipchart paper use
- Easy to move between rooms and setups
- Quick linking of multiple boards via "one-over-the-other" foot construction
- Tool-free mounting for fast and easy setup
- Magnetic enamel steel board surface using e³[™] CeramicSteel, which is Cradle to Cradle Certified® at the Bronze level
- Lifetime warranty on e³[™] CeramicSteel surface

Accessories

- Carry bag foldable workshop board+multiboard (Art.No. 7-230100)
- PROFESSIONAL whiteboard starter kit 77-piece (Art.No. 7-125500)
- SKETCH ECO paper pad grid 5x 20 sheets (Art.No. 7-157615)
- Push-pin assorted 200pcs (Art.No. 7-145299)
- Presentation marker TZ 41 assorted 4pcs set (Art.No. 7-155094)
- Presentation marker jumbo TZ 48 assorted 4pcs set (Art.No. 7-155594)

Art.No. 7-210510

GTIN 8713797109802



Article data sheet



Specifications

Height adjustable	No
Product material	Enamel steel
Surface (material/colour)	Whiteboard enamel steel / Dark grey
Frame (material/colour)	Aluminium / Black
Corner (material/colour)	Plastic / Black
Magnetic	Yes
Article dimensions	760 x 1200 x 22.1 mm
Castors	Yes
Number of castors	4
Number of lockable castors	4
Double sided	Yes
Pre printed	No
Included accessories	Click-on workshop paper hooks, Castors, Mounting materials
Surface warranty	99 years

Logistics

GTIN	8713797109802
Article number	7-210510
Customs tariff number	961000000000
Quantity	1 piece
Packing dimensions	785 x 97 x 1312 mm
Weight (gross/net)	12.74 kg / 9.81 kg
Country of origin	China

Article data sheet

Product overview

Article name	Article number	GTIN/EAN	Minimum order quantity
Legamaster PREMIUM PLUS mobile multiboard navy-blue feltboard	7-210410	8713797109819	1
Legamaster PREMIUM PLUS mobile multiboard grey feltboard	7-210510	8713797109802	1