

## D-Sub\_CCH\_S2\_PP\_PL\_PLA\_FC



Image is for illustration purposes only. Please refer to product description.

Part number	09 67 015 0210 160
Specification	D-Sub_CCH_S2_PP_PL_PLA_FC
HARTING eCatalogue	<a href="https://harting.com/09670150210160">https://harting.com/09670150210160</a>

### Identification

Category	Hoods / Housings
Series	D-Sub
Type of hood/housing	Shell housing
Description of hood/housing	Cover lockable

### Version

Size	D-Sub 2
Shielding	Shielded
Version	Top/side entry
Cable entry	3x
Cable fixing	Cable clamp
Locking type	PushPull
2 parts	Yes
Separable	Yes
Details	An external InduCom cable clamp or a crimp flange - ferrule combination can be used to gain more space in the housing.
Pack contents	2 blind plates internal cable clamp with screws

### Technical characteristics

Tightening torque	0.35 Nm Cable clamp screw
Ambient temperature	-20 ... +90 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP30



**Pushing Performance**  
Since 1945

## Technical characteristics

Cable diameter	3.3 ... 14 mm Please follow the assembly instructions!
Vibration resistance	Category 1B acc. to IEC 61373
Shock resistance	Category 1B acc. to IEC 61373

## Material properties

Material (hood/housing)	Thermoplastic
Surface (hood/housing)	Metallised
Colour (hood/housing)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	HB
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Commercial data

Packaging size	10
Net weight	19.68 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140469990
eCl@ss	27440213 D-Sub hood
UNSPSC 24.0	39121416