

Features

- Premium quality Nitrile (NBR) sheet made to stringent BS 2751 specifications
- Outstanding resistance to oils, fats and greases
- Best in class mechanical and physical properties
- Wide temperature Range: -30°C to 120°C

RS PRO Black BS 2751 Standard

Nitrile Rubber Sheet

1m x 1.4m x 3mm

RS Stock No.: 0205553



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

The RS PRO Nitrile Rubber (NBR) sheet is suitable for a wide range of industrial applications and environments and is well suited to the formation of gaskets, seals, hoses, tubing, protective sleeves and liners.

General Specifications

| | |
|------------------|----------------------|
| Colour | Black |
| Material | Nitrile Rubber (NBR) |
| Adhesive Backing | No |

Mechanical Specifications

| | |
|------------------|--------|
| Length | 1m |
| Width | 1.4m |
| Thickness | 3mm |
| Elongation | 250% |
| Tensile Strength | 13 MPa |
| Hardness | 70 ShA |

Operation Environment Specifications

| | |
|-------------------------------|-------|
| Maximum Operating Temperature | 70°C |
| Minimum Operating Temperature | -30°C |

Similar Products

| Stock No | Adhesive Backing | Thickness |
|----------|------------------|-----------|
| 0205553 | No | 3mm |
| 0205554 | No | 1mm |
| 0205556 | No | 1.5mm |
| 0205557 | No | 2mm |