



Fuse-link, low voltage, 20 A, AC 550 V, BS88, 21 x 129 mm, gL/gG, BS

Catalog No. **AD20**

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	20
Rated voltage			AC 550 V
Construction size			BS88
Size			21 x 129 mm
Utilization category			gL/gG
Breaking Capacity		kA	80
usable for size/applications			general industrial applications
Standard/Approval			BS
Shape			centre-bolted tags
Material			Ceramic body
Standards/Regulations			BS88-1 IEC 60269-1

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	20
Rated voltage		V	550
Voltage type			AC
Rated switching capacity		kA	80
Utilization category			gL/gG (cable protection/equipment protection)
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No

Additional product information (links)

Product datasheet (pdf)	http://www1.cooperbusmann.com/pdf/8bc57074-6978-45c3-91ea-417d851293f9.pdf
-------------------------	---