

FEATURES

- **Non-Releasable Design:** Ensures a secure hold that won't loosen over time
- **UV Resistant:** Suitable for outdoor use, resisting degradation from sunlight
- **High Tensile Strength:** Supports up to 18 kg, providing robust cable management
- **Wide Temperature Range:** Operates effectively from -40 °C to 85 °C, suitable for diverse conditions
- **RoHS Compliant:** Meets safety and environmental standards

RS PRO 150mm Nylon Cable Tie, Non-Releasable

RS Stock No: 656-093



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These RS PRO cable ties are designed for securing and organising cables efficiently. Made from durable nylon, they are ideal for use in various environments where a strong and reliable bundling solution is required.

General Specifications

Colour	Black
Product Type	Cable Tie
Sub Type	Non-Releaseable
Tensile Strength	18 kg

Protection Category

Fire Behaviour	UL 94HB
UV Resistant	Yes

Mechanical Specifications

Length	150 mm
Material	Nylon
Maximum Bundle Diameter	36 mm
Width	3.6 mm

Operation Environment Specifications

Maximum Operating Temperature	85 °C
Minimum Operating Temperature	-40 °C

Approvals

Standards/Approvals	RoHS, UL94HB
---------------------	--------------