

SylWork Flood Light

SylWork Flood BP 5000LM 840 IP65
0090001



Product features

- Slim LED portable work light
- Lightweight, slim, stylish robust,
- High-quality plastic body
- Stable, flexible positioning with stand or Tripod
- Option to use 2 work lights in the same time installed on the same Tripod
- Battery Operation - Battery running time & Lumen output: 90 minutes @ 1200lm, 5 hours @300lm, battery charging time: 4 hours
- Space-saving design - Tripod version can be folded up and stowed away
- 4000K Cool White light
- Total system efficacy up to 111lm/W
- CRI >80
- Operating temperature range: -20 to +40°C
- Lifetime: 30.000 hrs (L70/B50)
- 3 year warranty



PRODUCT OVERVIEW

Product name	SylWork Flood BP 5000LM 840 IP65
Technology	LED
General application	Residential & Consumer
ETIM Class	EC000346
Warranty	3 years
Light colour	Cool White
Photobiological Risk Group	RG1
Light source included	Fixture without Lightsource
Electrical protection	Class I
Dimmable	Yes
Dimming method	Onboard pot
IP rating	IP65
IK rating	IK07
Product EAN number	5410288900018

DATA TABLE

General data

Product name	SylWork Flood BP 5000LM 840 IP65
Technology	LED
General application	Residential & Consumer
ETIM Class	EC000346
Warranty	3 years

Optical data

Light colour	Cool White
Photobiological Risk Group	RG1

SylWork Flood Light

SylWork Flood BP 5000LM 840 IP65

0090001

Electrical data

Light source included	Fixture without Lightsource
Primary Supply/Product voltage - min (V)	220
Primary Supply/Product voltage - max (V)	240
Electrical protection	Class I
Dimmable	Yes
Dimming method	Onboard pot
Nominal Frequency (Hz)	50Hz

Physical data

IP rating	IP65
IK rating	IK07
Nominal Product Length (mm)	313
Nominal Product Width (mm)	226
Nominal Product Height (mm)	65
Weight (kg)	1.73

Packaging

Single packaging type	Carton
Product EAN number	5410288900018
Packaging single length / height (cm)	24.5
Packaging single width (cm)	33.0
Packaging single depth (cm)	7.5
DUN14 (outer)	15410288900015
Units per outer package	5
Packaging outer length / height (cm)	39.5
Packaging outer width (cm)	26.0
Packaging outer depth (cm)	35.0