

## FEATURES

- Oil-filled radiator
- Dimensions of 660 mm (H) x 370 mm (W) x 165 mm (D)
- Convection heating
- Floor mounted
- Thermostat control
- Three power settings
- British 3-pin plug
- Maximum output power of 1.5 kW
- Wheels for easy rolling transport

## 1.5kW Oil Filled Radiator, Floor Mounted, Type G - British 3-pin

RS Stock No.: 712-6061



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

For days when the room just doesn't get warm enough, turn to this 1.5 kW oil-filled radiator. Slim and easy to move, it has adjustable thermostatic controls to quickly heat a space to the desired temperature.

With wheels on the base for transport, it's easy to move the heater to where it's needed. Ideal for warming confined spaces, it's electrically powered and has much lower running costs than central heating. It also features excellent thermal retention, so less energy is needed to top up temperatures.

## General Specifications

<b>Heat Type</b>	Convection
<b>Control Type</b>	Thermostat
<b>Power Settings</b>	1
<b>Safety Thermostat</b>	Yes
<b>Thermal oil</b>	Yes
<b>Applications</b>	Automobile workshop, Construction area, Assembly operation, Food and beverage, Storeroom and workshop, Greenhouse

## Electrical Specifications

<b>Maximum Output Power</b>	1.5KW
<b>Voltage Rating</b>	220V to 240V
<b>Frequency</b>	50Hz
<b>Plug Type</b>	Type G - British 3-pin

## Mechanical Specifications

<b>Mounting</b>	Floor Mounted
<b>Dimensions</b>	660mm x 370mm x 165mm
<b>Height</b>	660mm
<b>Width</b>	370mm
<b>Depth</b>	165mm

## Approvals

<b>Compliance/Certifications</b>	ANSI/ESD S20.20:2014, BS EN 61340-5-1:2007, RoHS
----------------------------------	--