

LED LENSER® X7R

This ultra-powerful rechargeable hand torch from German world leaders LED Lenser has two separate lens housings, each containing a super-strength LED capable of immense light output and a wider, more intense beam. Together they blast out a maximum of 500 lumens for illumination up to 320 metres. On the side of the torch a smooth-action sliding head pilots down from distant spot beam to a focused flood beam, this a monumental 45 metres in diameter. Light quality is fantastic because of the integral Advance Focus System optics, which govern and direct the light more consistently and efficiently. With the additional benefit of integrated micro-chip controlled Smart Light Technology, the user has two energy modes, three light programmes and eight different light functions to call upon. These include Boost, Dim, SOS and self-defence Strobe, an effective personal safety feature. One might expect these features to sap power but that's where the excellent Floating Charge System can save money and time: it enables charging without fiddly battery removal. Simply attach the whole torch to the magnetic charger and away you go. The X7R is both economical and eco-friendly. The aluminium barrel casing offers great protection and outstanding durability. The torch is supplied with a wrist strap, belt clip plus 1 x L-ion 3.7v battery and full mains/USB charger set in a durable protective hard case.

As a leading international brand of hand-held torches and head lamps, LED Lenser is renowned for superior German engineering, outstanding performance, and state-of-the art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class- leading lighting instruments, LED Lenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. LED Lenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient CREE LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability that is second to none.

- Medium sized, dual lens LED hand-held torch with advanced optics.
- Energy efficient CREE® Xtreme LED Light Chips
- State-of-the-art, reliable German engineering
- Advanced Focus System™ Optics. Patented reflector and lens combination for intense spot (distance) or flawless flood (near) illumination
- Smart Light Technology™. Micro-chip controlled multi-option technology. Two energy usage modes, three pre-set light programs and eight light options (Morse, Dim, Boost, Power, Low Power, Blink, SOS, Defence Strobe)
- X-Lens Technology™. Multiple lenses perfectly calibrated to produce an awesome single beam
- Dynamic Switch™ - Reactive, single switch control
- Large beam width due to larger head size
- Robust, yet lightweight aircraft-grade aluminium housing
- User-friendly modular design
- Corrosion resistant gold plated contacts for better conductivity
- Water and dust resistant. IPX54

Technical Information

Size: 171 x 70mm Ø

Power: 500 lumens max

Run Time: up to 7.5 hours

Beam Distance: up to 320m

Weight: 240grams

Supplied with : Hard Case, Mains Charger, USB cable, Wall Mount, Wrist-strap, 360° Belt Clip and Rechargeable Battery (1xL-ion 3.7v)

Code	Colour	Packaging	Barcode
8408R	Black	Case	4029113840835