

Features

- Ideal to work in Hard-to-Reach Areas
- Used for finishing, removing weld seams, burrs, and defects on surfaces like metal and wood.
- Slotted rubber construction improves airflow and temperature resistance while securely fixing the abrasive.
- Suitable for both pneumatic and portable power tools.

RS PRO Backing Pads & Mandrels

RS Stock No.: 0768413, 0768415, 0768417, 0768231, 0768233, 0768235, 0768237, 0768241, 0768242, 0768244, 0768248, 0768249, 0768252



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Expanding rubber holders are the ideal solution for working in hard-to-reach areas. They are primarily used for finishing, removing weld seams, burrs, and other defects from various surfaces such as metal and wood.

Their special slotted rubber design ensures better airflow and increased temperature resistance, while simultaneously securely fixing the abrasive material in place (which must be purchased separately).

Featuring durable 6 mm metal shafts, these drum holders are compatible with both pneumatic tools and portable power tools.

General Specifications

Holder Types	Cylindrical (D x H x S) and Conical (D1 x D2 x H x S)
Shaft Diameter (S)	6 mm

Mechanical Specifications

A. Cylindrical Rubber Mandrels (Compatible with cylindrical sanding drums)

Article Code	Dimensions (D x H x S) [mm]	Maximum Speed [min ⁻¹]	Compatible Cylindrical Sanding Drum Size
0768413	15 x 30 x 6	26000	15 x 30
0768415	19 x 25 x 6	20000	19 x 25
0768417	22 x 20 x 6	17000	22 x 20
0768231	25 x 25 x 6	15000	25 x 25
0768233	30 x 20 x 6	13300	30 x 20
0768235	30 x 30 x 6	13300	30 x 30
0768237	38 x 25 x 6	11000	38 x 25
0768241	45 x 30 x 6	8500	45 x 30
0768242	51 x 25 x 6	7000	51 x 25
0768244	60 x 30 x 6	6500	60 x 30

B. Conical Rubber Mandrels (Compatible with conical sanding drums)

Article Code	Dimensions (D1 x D2 x H x S) [mm]	Maximum Speed [min ⁻¹]	Compatible Conical Sanding Drum Size
0768248	20 x 14 x 63 x 6	13000	20 x 14 x 63
0768249	29 x 22 x 30 x 6	13000	29 x 22 x 30
0768252	36 x 22 x 60 x 6	5000	36 x 22 x 60