

## Han 16B HBM Rear-Fit DL



Part number	09 30 016 0391
Specification	Han 16B HBM Rear-Fit DL
HARTING eCatalogue	<a href="https://b2b.harting.com/09300160391">https://b2b.harting.com/09300160391</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han® B
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Rear mounting
Type	Low construction

### Version

Locking type	Double locking lever
Han-Easy Lock®	Yes
Size	16 B
Field of application	Standard hoods/housings for industrial connectors
Pack contents	Mounting frame is included within the delivery

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP66
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)



Pushing Performance

## Material properties

Material (seal)	NBR
Material (locking)	Polycarbonate Stainless steel
Colour (locking)	RAL 7037 (dust grey)
Material (accessories)	Polyamide Stainless steel
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	1
Net weight	122.1 g
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors